

GCC TOOL LIST

laser line machine and the accessories

Red laser line machine **LS-168R**

(4V1H1D) 10 meters in 1mm tolerance



MULTI LINE LASER

Green laser line machine **LS-168G**

(4V1H1D) 10 meters in 1mm tolerance



MULTI LINE LASER

Elevator Tripod TP-165 & EXT150



Laser Meter LM-60



Hole Drilling Bit



Φ6mm, Φ8mm, Φ10mm, Φ20mm, Φ25mm


3 Ways Hex Wrench HW-001



Drilling mold for GCC SWS & SFW systems

For SFW-DR system

For SWS-DR system






GB-814 GLASS SEAL




Cautions

- ⚠ Do not use soap-based cleaner.
- ⚠ Use alcohol cleaning wipe to clean the glass.



GB-01T Template

- * The template GB-01T is by order.
- * For sliding door & bi-folding door use.



GOOD CREDIT CORPORATION

<http://www.gccintw.com.tw> E-mail: gcctw@ms7.hinet.net

TEL: 886-4-22583755 (Hunting Line) FAX: 886-4-22583753 No.13, Longmen Rd., Situn Dist., Taichung 40757, Taiwan




Member
NGA
National Glass
Association




GB-814 GLASS SEAL




Application




For sliding door system use.



GB-814
(with adhesive tape)



For bi-folding system use.



Soft material



GOOD CREDIT CORPORATION

<http://www.gccintw.com.tw> E-mail: gcctw@ms7.hinet.net

TEL: 886-4-22583755 (Hunting Line) FAX: 886-4-22583753 No.13, Longmen Rd., Situn Dist., Taichung 40757, Taiwan



Member
NGA
National Glass
Association